# atena

 $space \cdot colour \cdot organization$ 





### atena **mini**

Atena has been designed to fit into the tightest rooms and create the best working environment. The essential is there, where it is supposed to be.

# 1 2 3

#### operational areas

collection decontamination

clean area

1. AT34A 50cm 2. AT03A 50cm 3. AT72 60cm








# atena **regular**

Cleaning and disinfection area gains a wider space thanks to the 80cm module with drawers and internal dividers, together with the mobile unit for autoclaves. The storage area increases as well, both inside the 80cm module and the wall cabinets.


#### operational areas

collection decontamination clean area



1. AT34A 50cm 2. AT03A80 80cm 3. AT40 60cm 4. AT01 50cm





1. W60cm worktop 4. AT03A 50cm 2. AT01 50cm 5. AT03A 50cm

3. AT34A 50cm 6. AT01 50cm

# atena **large**

Moving between any operational area has never been so effective. Friday comes first, to collect infected materials from every cabinet. We move then to the sink instaled in the worktop, to clean infected instruments and equipments. Last but not least, we place sterile instruments and equipments in the storage modules and wall cabinets.

#### operational areas

collection decontamination clean area






Stainless steel paper roll holder (ACS76)





Electrical opening 80cm module with internal dividers for drawers



Stainless steel holder with infrared distributor for

soap/disinfectant (ACS78)

Stainless steel holder for disinfector cleaners (ACS72) W34 x H 28 x D22.5cm Stainless steel holder for special waste (ACS75)




# atena **full**

The most equipped version of the Atena line. Accessories and equipments find their place in the splashback panel, including special waste bin and ultrasonic cleaner.

Autoclave and thermosealing machine column sets the border between dirty and clean areas, and guarantees easy access to both thanks to its lower position.

# 



- 1. AT01E 60cm
- 2. AT34A 50cm
- 3. W60cm worktop
- 4. AT03A80 80cm
- 5. AT74 60cm
- 6. AT01 50cm



